




PRESSALIT®

Product Item number	CareSystem shower chair 410 with aperture, manually height adjustable R7168000
Colour Product description	<div>  </div> White Shower chair 410 with aperture "soft feel", with back rest and arm supports, seat height adjustable 340 mm. Excl. mounting kit. Discontinued as per 31/12-2015 Shower chair 410 with aperture "soft feel", with back rest and arm supports, seat height adjustable 340 mm. Excl. mounting kit. Discontinued as per 31/12-2015
Adjustability Product capacity	Height adjustable Max. vertical load: 150 kg.
Materials	Basic material: 20 micrometre anodized aluminium Seat/backrest: Polyurethane foam with marine ply core Seat/backrest surface: Gum lac Armrest surface: Two-component plastic (PVC) End cap, armrest: Arnite Lever: Stainless steel w/nylon knob Front plate/end covers, track: Polystyrene plastic (PS)



PRESSALIT®

Product Item number	CareSystem shower chair 410 with aperture, manually height adjustable R7168000
Ergonomy	The armrests' oval shape gives an easy and comfortable surface to lean and push against. Soft and slip-resistant material with a warm feel. Ergonomically designed seat with aperture that makes intimate hygiene easier.
Features	The seat and armrests can fold up when not in use or to make more space. Height adjustable 340 mm - the height of the seat and the backrest can be adjusted separately.
Cleaning	Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in clear water.

pressalit.com