





PRESSALIT®

Product Item number	Lift for countertop, electrically height adjustable RK1710
Product description	<p>EAN:5708590265926</p>   <p>The name INDIVO relates to the individual configuration of the products.</p> <p>Lift for countertop, with 2 motors and switches. Including 2 brackets and transformer. Lengths from 23.6" - 39.4". Height adjustable up to 11.8". Incl. mounting kit for brick wall Please state desired length when ordering</p>
Adjustability Adjustment height Product capacity Speed up Noise level	<p>Height adjustable</p> <p>11,82 inch</p> <p>Maximum load (evenly distributed): 220 lbs including countertop.</p> <p>Speed up: 0,79 inch/s Speed down: 0,79 inch/s</p> <p>45 dB</p>
Materials	<p>Material:</p> <p>Telescopic leg: Aluminium, ABS plastic Cross braces: Aluminium Brackets: Steel Cable tray: ABS plastic Switches: ABS plastic Surface treatment: Brackets: Powder lacquered (grey RAL 9006)</p>



Product	Lift for countertop, electrically height adjustable
Item number	RK1710
Ergonomy	<p>An electric height-adjustable kitchen countertop is ideal in all situations where various users - both seated and standing - use the same kitchen.</p> <p>This is equally true in private homes as well as larger centers with common kitchen facilities such as group homes and care centers.</p>
Features	<p>Lift heights are adjusted via switches in the front edge.</p> <p>Operating switches can be placed wherever you want in the front edge.</p> <p>The switches are color-coded - aluminium to operate countertops and red to operate wall cabinets.</p> <p>Lifts can be adapted to most standard kitchen components.</p> <p>Lifts are available for countertops of any length between 23.6" and 118.1".</p>
Actuator (motor)	DB4 Deskline (Linak) 1000 N, IP22
Control box	CBD6 (Linak), IP22
Wired remote control	HB53 (Linak), IPX1
Warranty	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.</p>



PRESSALIT®

Product	Lift for countertop, electrically height adjustable
Item number	RK1710
Cleaning	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that water deposits (Calcium, lime etc.) be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in plain water.</p>



PRESSALIT®

Product	Lift for countertop, electrically height adjustable
Item number	RK1710

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®