



# PRESSALIT®

<b>Product</b> <b>Item number</b>	Touchless faucet RT631
<b>Product description</b>	VVS:704388104 NRF:6132551 EAN:5708590297354 HMI: 123754 NBS:N13:30,335  Touchless faucet with a temperature adjustment handle. WRAS-approved. We recommend T4679 plumbing kit with 0.4" compatible adaptor.  Touchless faucet with a temperature adjustment handle. WRAS-approved. We recommend T4679 plumbing kit with 0.4" compatible adaptor.
<b>Features</b>	Temperature adjustment. Battery-operated 6 V. Flow controller (5 l/min.) Infrared sensor technology Protection against scalding
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
<b>Cleaning</b>	This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.

[pressalit.com](http://pressalit.com)