




<b>Product</b> <b>Item number</b>	PLUS shower seat 450, manually height adjustable R7420182000
<b>Color</b>	VVS:777535500 NRF:6311165 EAN:5708590311609 HMI: 71801 NBS:N13:448 FDA:INN/D135865 White
<b>Product description</b>	 <p>PLUS shower seat 450, with backrest. Manually height adjustable by 14.2" . The seat and is foldable. Pale gray cover plate for vertical wall track.          Materials: Comfortable polyurethane foam over a plywood core, fitted to an aluminium profile.          Excl. mounting kit.</p> <p>PLUS shower seat 450, with backrest. Manually height adjustable by 14.2" . The seat and is foldable. Pale gray cover plate for vertical wall track.          Materials: Comfortable polyurethane foam over a plywood core, fitted to an aluminium profile.          Excl. mounting kit.</p>
<b>Adjustability</b> <b>Adjustment height</b> <b>Product capacity</b>	Height adjustable 14,18 inch Maximum user mass: 440 lbs. When the seat is loaded with 440 lbs, each wall fastener is loaded with 40 lbs. <i>The seat has been tested statically with safety factor 1.5, which is a requirement according to the applied assistive products standards.</i>
<b>Materials</b> <b>Ergonomy</b>	The shower seat is made of polyurethane (PU) foam with a plywood core and this is covered with a moulded coated surface that is protected using a clear PU lacquer. The backrest is made of polyurethane (PU) foam protected using a clear PU lacquer. Internal components and fasteners are primarily made of stainless steel. The hinge barrel is capped with ABS. Ergonomically designed seat - contact surface are 17.7" x 17.2". Soft and slip-resistant material that has a warm feel.



# PRESSALIT®











<b>Product</b>	PLUS shower seat 450, manually height adjustable
<b>Item number</b>	R7420182000
<b>Features</b>	The seat can fold up when not in use or to maximize floor space. The seat and backrest can be adjusted simultaneously thanks to a safe and easy click system.
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
<b>Cleaning</b>	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: CaviCide</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that water deposits (Calcium, lime etc.) be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in plain water.</p>



PRESSALIT®













<b>Product</b>	PLUS shower seat 450, manually height adjustable
<b>Item number</b>	R7420182000

## Mounting in different wall types

	<b>Concrete &gt;B25</b> V8612 - Mounting kit, 10 lag bolts Ø8 x 70, plugs SX10. To be ordered separately.	
	<b>Solid Brick &gt;= Mz12</b> V8612 - Mounting kit, 10 lag bolts Ø8 x 70, plugs SX10. To be ordered separately.	
	<b>Solid Sand Lime Brick &gt;= Hlz12</b> V8612 - Mounting kit, 10 lag bolts Ø8 x 70, plugs SX10. To be ordered separately.	
	<b>Aerated Concrete P4</b> V8662 - Mounting kit, 10 countersunk bolts M8 x 35, plugs FTP M 8. To be ordered separately.	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b> V8612 - Mounting kit, 10 lag bolts Ø8 x 70, plugs SX10. NB! Plugs are not needed. To be ordered separately.	



# PRESSALIT®

<b>Product</b> <b>Item number</b>	PLUS shower seat 450, manually height adjustable R7420182000		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Wall fasteners (10 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.	  	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b> Wall fasteners (10 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.	  	
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Wall fasteners (10 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.	  	

pressalit.com

# PRESSALIT®