



# PRESSALIT®

<b>Product</b> <b>Item number</b>	MATRIX ANGLE sink without overflow, right-facing R2041000
<b>Color</b>	VVS:636856000 NRF:6132508 EAN:5708590325118 HMI: 82615 NBS:N13:30,335 White
<b>Product description</b>	<p>MATRIX is a series of sinks, most of them are designed by Pressalit. MATRIX SMALL and CURVE sinks fit onto PLUS, SELECT and VALUE sink brackets, whereas MATRIX MEDIUM and ANGLE are tailor made to fit specific brackets.</p> <p>MATRIX ANGLE vanity sink, 39.4" x 22.4" x 4.7", right-facing, with two integrated grab handles in the front, with tap hole diameter 1.4", without overflow, incl. drain fitting. The sink has raised edges, preventing water from running over the back or down the outer sides.</p> <p>Materials: Cultured marble with a high-polished, nonporous sanitary gel coating. Suitable for R2015 height adjustable sink supports.</p>
<b>Product capacity</b>	440 lbs.
<b>Materials</b>	Cultured marble with a high-polished, nonporous sanitary gel coating.
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.



<b>Product</b>	MATRIX ANGLE sink without overflow, right-facing
<b>Item number</b>	R2041000
<b>Cleaning</b>	<p>For cleaning the wash basin, use hot water and a mild soapy cleaning agent. Make sure that the product is wiped down with a soft rag wrung out in clear water immediately after cleaning.</p> <p>For disinfecting the wash basin, the following agents can be used:</p> <p>Sodium hydroxide 5%</p> <p>Acetic acid solution 10%</p> <p>Ethanol solution 70%</p> <p>Sodium hypochlorite 5%, active chlorine</p> <p>Sodium chloride 170g/l, diluted to 50%.</p> <p>Make sure that the product is wiped down with a soft rag wrung out in clear water immediately after disinfection.</p> <p><b>NB! Do not use abrasive cleaning agents, as this will cause damage to the surface of the wash basin.</b></p>
<b>Declaration of conformity</b>	<p><b>Declaration of Performance</b></p> <p>Compliance criteria according to EN 14688:2015.</p> <p>4.1 Load resistance: stable, without cracks or deformations.</p> <p>4.2 Draining of water: Water drained away completely.</p> <p>4.3 Resistance to temperature changes: Without cracks, delaminations.</p> <p>4.4 Resistance to chemicals and staining agents:</p> <ul style="list-style-type: none"><li>- Sodium hydroxide 5% - without staining or deterioration;</li><li>- Acetic acid solution 10% - without staining or deterioration;</li><li>- Ethanol sol. 70% - without staining or deterioration;</li><li>- Sodium hypochlorite 5% active chlorine - without staining or deterioration;</li><li>- Sodium chloride 170g/l diluted to 50% - without staining or deterioration.</li></ul> <p>4.5 Surface stability / resistance to scratching: Do not use abrasives on the surface.</p> <p>4.6 Cleanability: Smooth, non-absorbant surfaces.</p> <p>4.7 Protection against overflowing: CL 00.</p> <p>4.8 Durability: Product is considered durable.</p>