



PRESSALIT®

Product Item number	MATRIX CURVE II ergonomic sink with tap hole, without overflow R2053000
Color	VVS:636862200 NRF:6132514 RSK:7503002 EAN:5708590333878 HMI: 101016 White
Product description	<p>MATRIX is a series of sinks, most of them are designed by Pressalit. MATRIX SMALL and CURVE sinks fit onto PLUS, SELECT and VALUE sink brackets, whereas MATRIX MEDIUM and ANGLE are tailor made to fit specific brackets.</p> <p>MATRIX CURVE II ergonomic sink, 23.6" x 19.2" x 5.9", with tap hole diameter 1.4", without overflow. Supplied with drain fitting. The concave front edge stabilises standing as well as seated users. The rounded edges are also comfortable to hold and rest against. The flat bottom leaves room for the legs underneath. Material: Ceramic. Suitable for sink brackets from the Pressalit PLUS, SELECT and VALUE ranges.</p>
Product capacity	330 lbs.
Materials Ergonomy	Ceramic The concaved front edge stabilizes a standing as well as a seated user. The rounded shapes are nice to grip and lean against. The design of the corners leaves space and supports the elbows in the sink and the flat bottom leaves space for the legs of a seated user.
Warranty Cleaning	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use corrosive cleaners. For surface disinfection, chlorine based agents can be used if diluted according to specifications.</p>



PRESSALIT®











Product	MATRIX CURVE II ergonomic sink with tap hole, without overflow
Item number	R2053000
Declaration of conformity	<p>Declaration of Performance</p> <p>Compliance criteria according to EN 14688:2015.</p> <p>4.1 Load resistance: Pass.</p> <p>4.2 Draining of water: Pass.</p> <p>4.3 Resistance to temperature changes: Pass.</p> <p>4.4 Resistance to chemicals and staining agents: Pass.</p> <p>4.5 Surface stability / resistance to scratching: Pass.</p> <p>4.6 Cleanability: Pass.</p> <p>4.7 Protection against overflow: CL 00.</p> <p>4.8 Durability: Pass.</p>



PRESSALIT®







Product	MATRIX CURVE II ergonomic sink with tap hole, without overflow
Item number	R2053000

Mounting in different wall types

	Concrete >B25 V8602 - Mounting kit, 2 lag bolts Ø10 x 100 - plugs SX12. To be ordered separately	
	Solid Brick >= Mz12 V8602 - Mounting kit, 2 lag bolts Ø10 x 100 - plugs SX12. To be ordered separately	
	Solid Sand Lime Brick >= Hlz12 V8602 - Mounting kit, 2 lag bolts Ø10 x 100 - plugs SX12. To be ordered separately	
	Aerated Concrete P4 V8652 - Mounting kit, 2 lag bolts Ø10 x 100 - plugs GB14. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8602 - Mounting kit, 2 countersunk bolts Ø10 x 80, plugs SX12. NB! Plugs are not needed. To be ordered separately.	



PRESSALIT®

Product Item number	MATRIX CURVE II ergonomic sink with tap hole, without overflow R2053000
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 

It is the responsibility of the installer to ensure that suitable wall fasteners are used.

pressalit.com