



PRESSALIT®

Product Item number	Changing table, 31.5" x 70.9", electrically height adjustable R8643000
Color	VVS:777637030 NRF:7501968 EAN:5708590338309 HMI: 48879 White
Product description	<p>Pressalit offers a wide variety of changing tables designed for use in daycare facilities. The tables are available in several sizes and models, either free standing or wall-hung. The fold away feature in wall-hung tables is useful where space is limited. The wall-hang tables with low start are essential for daycare or preschool facilities. Even toddlers can climb onto the table themselves, without the staff lifting them.</p> <p>Changing table, freestanding, 31.5" x 70.9". With motor and transformer, height adjustable from 25.6" - 39.4", with hand control. Laminate worktop, incl. 2 wire baskets. Materials: Laminate and powder-lacquered steel.</p>
Adjustability Adjustment height Product capacity Speed up Noise level	Height adjustable 13,79 inch Max load: 330 lbs. Speed up: 0,55 inch/s Speed down: 0,55 inch/s 48 dB
Materials Ergonomy Features Mains connection (V)	Lifting unit and baskets: Powder-coated steel. Countertop: Melamine. The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height. Easy-to-clean surfaces ensure optimum hygiene. 230



PRESSALIT®

Product	Changing table, 31.5" x 70.9", electrically height adjustable
Item number	R8643000
Actuator (motor)	2 x LA31 Deskline (Linak), 1500N, IPX1
Control box	CBD6 (Linak), IP20
Wired remote control	HB30 (Linak), IPX4
Power consumption (maximum load)	Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
Cleaning	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>



PRESSALIT®

Product	Changing table, 31.5" x 70.9", electrically height adjustable
Item number	R8643000

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®