




PRESSALIT®

Product Item number	Changing table, 31.5" x 70.9", electrically height adjustable, with sanitary appliances R8653000
Color	VVS: 777637230 NRF: 7501971 EAN: 5708590338323 HMI: 48881 White
Product description	 <p>Pressalit offers a wide variety of changing tables designed for use in daycare facilities. The tables are available in several sizes and models, either free standing or wall-hung. The fold away feature in wall-hung tables is useful where space is limited. The wall-hang tables with low start are essential for daycare or preschool facilities. Even toddlers can climb onto the table themselves, without the staff lifting them.</p> <p>Changing table, freestanding, with sink/faucet, 31.5" x 70.9". With motor and transformer, height adjustable from 25.6" - 39.4", with hand control. Laminate worktop with inset stainless steel sink, incl. lever operated faucet, pull-out shower head, feed/waste system and 2 wire baskets. Materials: Laminate and powder-lacquered steel.</p>
Adjustability	Height adjustable
Adjustment height	13,79 inch
Product capacity	Max load: 330 lbs.
Speed up	Speed up: 0,55 inch/s Speed down: 0,55 inch/s
Noise level	48 dB
Materials	Lifting unit and baskets: Powder-coated steel. Countertop: Melamine. Waste pipe: Polyurethane, PVC and steel. The flexible waste pipe is very resistant to both chemical and physical influences. It is flame retardant and withstands temperatures from -30°C to +110°C.
Ergonomy	The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height.



PRESSALIT®

Product	Changing table, 31.5" x 70.9", electrically height adjustable, with sanitary appliances
Item number	R8653000
Features	Easy-to-clean surfaces ensure optimum hygiene. Undermount sink and tap with pull-out spout.
Mains connection (V)	230
Actuator (motor)	2 x LA31 Deskline (Linak), 1500N, IPX1
Control box	CBD6 (Linak), IP20
Wired remote control	HB30 (Linak), IPX4
Power consumption (maximum load)	Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
Cleaning	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: CaviCide</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>

pressalit.com

PRESSALIT®