



PRESSALIT®

Product Item number	Changing table, 31.5" x 55.1", electrically height adjustable, with sanitary appliances R8654000
Color Product description	VVS: 777637320 NRF: 7501972 EAN: 5708590338330 HMI: 100174 White <p>Pressalit offers a wide variety of changing tables designed for use in daycare facilities. The tables are available in several sizes and models, either free standing or wall-hung. The fold away feature in wall-hung tables is useful where space is limited. The wall-hang tables with low start are essential for daycare or preschool facilities. Even toddlers can climb onto the table themselves, without the staff lifting them.</p> <p>Changing table, freestanding, with sink/faucet, 35.5" x 55.1". With motor and transformer, height adjustable from 25.6" - 39.4", with hand control. Molded worktop with integrated sink, incl. lever operated faucet, feed/waste system and 2 wire baskets. Materials: ABS plastics, synthetic acrylic and powder-lacquered steel.</p>
Adjustability Adjustment height Product capacity Speed up Noise level	Height adjustable 13,79 inch Max load: 165 lbs. Speed up: 0,55 inch/s Speed down: 0,55 inch/s 48 dB
Materials Ergonomy	Lifting unit and baskets: Powder-coated steel. Countertop: ABS with acrylic. Waste pipe: Polyurethane, PVC and steel. The flexible waste pipe is very resistant to both chemical and physical influences. It is flame retardant and withstands temperatures from -30°C to +110°C. The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height.



Product	Changing table, 31.5" x 55.1", electrically height adjustable, with sanitary appliances
Item number	R8654000
Features	Easy-to-clean surfaces ensure optimum hygiene. Integrated sink and tap.
Mains connection (V)	230
Actuator (motor)	LA31 Deskline (Linak), 1500N, IPX1
Control box	CBD6 (Linak), IP20
Wired remote control	HB30 (Linak), IPX4
Power consumption (maximum load)	Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
Cleaning	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>



PRESSALIT®

Product	Changing table, 31.5" x 55.1", electrically height adjustable, with sanitary appliances
Item number	R8654000

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®