



# PRESSALIT®

<b>Product</b> <b>Item number</b>	Changing table, 31.5" x 55.1", electrically height adjustable, foldable R8672000
<b>Color</b>	VVS:777636120 NRF:7501978 EAN:5708590338392 HMI: 48573  White
<b>Product description</b>	<p>Pressalit offers a wide variety of changing tables designed for use in daycare facilities. The tables are available in several sizes and models, either free standing or wall-hung. The fold away feature in wall-hung tables is useful where space is limited. The wall-hang tables with low start are essential for daycare or preschool facilities. Even toddlers can climb onto the table themselves, without the staff lifting them.</p> <p>Changing table, wall-mounted, low start, foldable, 31.5" x 55.1". With motor and transformer, height adjustable from 11.8" - 39.4", with hand control. Materials: Molded worktop in ABS plastics, synthetic acrylic and powder-lacquered steel. Excl. fixing kit.</p>
<b>Adjustability</b> <b>Adjustment height</b>  <b>Product capacity</b>  <b>Speed up</b>  <b>Noise level</b>	Height adjustable  27,58 inch  Max load: 165 lbs.  Speed up: 1,5 inch/s Speed down: 1,5 inch/s  48 dB
<b>Materials</b>  <b>Ergonomy</b>	Lifting unit: Powder-coated steel. Countertop: ABS with acrylic.  The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height. The table descends to a very low position, which offers the advantage that toddlers can easily climb up and down themselves. Thereby unnecessary lifting is avoided.



# PRESSALIT®











<b>Product</b> <b>Item number</b>	Changing table, 31.5" x 55.1", electrically height adjustable, foldable R8672000
<b>Features</b>  <b>Mains connection (V)</b>  <b>Actuator (motor)</b>  <b>Control box</b>  <b>Wired remote control</b>  <b>Power consumption (maximum load)</b>	Easy-to-clean surfaces ensure optimum hygiene. The integrated pneumatic cylinder enables the table to be folded easily against the wall when not in use to maximize floor space. Integrated safety system prevents entrapment.  230  LA31 Deskline (Linak), 2500N, IPX1  CBD6 (Linak), IP20  HB30 (Linak), IPX4  Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W
<b>Warranty</b>  <b>Cleaning</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.  This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.  The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.  DISINFECTANTS: CaviCide  The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.



PRESSALIT®











<b>Product</b>	Changing table, 31.5" x 55.1", electrically height adjustable, foldable
<b>Item number</b>	R8672000

## Mounting in different wall types

	<p><b>Concrete &gt;B25</b></p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p><b>Solid Brick &gt;= Mz12</b></p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p><b>Solid Sand Lime Brick &gt;= Hlz12</b></p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p><b>Aerated Concrete P4</b></p> <p>V8658 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs GB14. To be ordered separately.</p>	
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b></p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.</p>	



# PRESSALIT®

Product Item number	Changing table, 31.5" x 55.1", electrically height adjustable, foldable R8672000		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.	  	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b> Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.	  	
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

pressalit.com