




PRESSALIT®

Product Item number	Changing table, 31.5" x 55.1", electrically height adjustable, with sanitary appliances R8682000
Color	VVS: 777636220 NRF: 7501981 EAN: 5708590338415 HMI: 48564 White
Product description	 <p>Pressalit offers a wide variety of changing tables designed for use in daycare facilities. The tables are available in several sizes and models, either free standing or wall-hung. The fold away feature in wall-hung tables is useful where space is limited. The wall-hang tables with low start are essential for daycare or preschool facilities. Even toddlers can climb onto the table themselves, without the staff lifting them.</p> <p>Changing table, wall-mounted, low start, with sink/faucet, 31.5" x 55.1". With motor and transformer, height adjustable from 11.8" - 39.4", with hand control and safety stop function. Molded worktop with integrated sink, incl. lever operated faucet, pull-out shower head, feed/waste system and 2 wire baskets. Materials: ABS plastics, synthetic acrylic and powder-lacquered steel. Excl. fixing kit.</p>
Adjustability	Height adjustable
Adjustment height	27,58 inch
Product capacity	Max load: 165 lbs.
Speed up	Speed up: 1,5 inch/s Speed down: 1,5 inch/s
Noise level	48 dB
Materials	Lifting unit and baskets: Powder-coated steel. Countertop: ABS with acrylic.
Ergonomy	The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height. The table descends to a very low position, which offers the advantage that toddlers can easily climb up and down themselves. Thereby unnecessary lifting is avoided.



PRESSALIT®











Product	Changing table, 31.5" x 55.1", electrically height adjustable, with sanitary appliances
Item number	R8682000
Features	Easy-to-clean surfaces ensure optimum hygiene. Integrated sink and tap with pull-out spout. Integrated safety system prevents entrapment.
Mains connection (V)	230
Actuator (motor)	LA31 Deskline (Linak), 2500N, IPX1
Control box	CBD6 (Linak), IP20
Wired remote control	HB30 (Linak), IPX4
Power consumption (maximum load)	Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
Cleaning	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: CaviCide</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>



PRESSALIT®







Product	Changing table, 31.5" x 55.1", electrically height adjustable, with sanitary appliances
Item number	R8682000

Mounting in different wall types

	Concrete >B25 V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.	
	Solid Brick >= Mz12 V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.	
	Aerated Concrete P4 V8658 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs GB14. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.	



PRESSALIT®

Product Item number	Changing table, 31.5" x 55.1", electrically height adjustable, with sanitary appliances R8682000
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar. 
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar. 
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 

pressalit.com