




PRESSALIT®

Product Item number	Changing table, 31.5" x 70.9", electrically height adjustable, with sanitary appliances R8683000
Color	VVS: 777636230 NRF: 7501982 EAN: 5708590338422 HMI: 48576 White
Product description	 <p>Pressalit offers a wide variety of changing tables designed for use in daycare facilities. The tables are available in several sizes and models, either free standing or wall-hung. The fold away feature in wall-hung tables is useful where space is limited. The wall-hang tables with low start are essential for daycare or preschool facilities. Even toddlers can climb onto the table themselves, without the staff lifting them.</p> <p>Changing table, wall-mounted, low start, with sink/faucet, 31.5" x 70.9". With motor and transformer, height adjustable from 11.8" - 39.4", with hand control and safety stop function. Laminate worktop with inset stainless steel sink, incl. lever operated faucet, pull-out shower head, feed/waste system and 2 wire baskets. Materials: Laminate and powder-lacquered steel. Excl. fixing kit.</p>
Adjustability	Height adjustable
Adjustment height	27,58 inch
Product capacity	Max load: 165 lbs.
Speed up	Speed up: 1,5 inch/s Speed down: 1,5 inch/s
Noise level	48 dB
Materials	Lifting unit and baskets: Powder-coated steel. Countertop: Melamine. Waste pipe: Polyurethane, PVC and steel. The flexible waste pipe is very resistant to both chemical and physical influences. It is flame retardant and withstands temperatures from -30°C to +110°C.













Product Item number	Changing table, 31.5" x 70.9", electrically height adjustable, with sanitary appliances R8683000
Ergonomy Features Mains connection (V) Actuator (motor) Control box Wired remote control Power consumption (maximum load)	<p>The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height. The table descends to a very low position, which offers the advantage that toddlers can easily climb up and down themselves. Thereby unnecessary lifting is avoided.</p> <p>Easy-to-clean surfaces ensure optimum hygiene. Undermount sink and tap with pull-out spout. Integrated safety system prevents entrapment.</p> <p>230</p> <p>LA31 Deskline (Linak), 3500N, IPX1</p> <p>CBD6 (Linak), IP20</p> <p>HB30 (Linak), IPX4</p> <p>Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W</p>
Warranty Cleaning	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.</p> <p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: CaviCide</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>



Product	Changing table, 31.5" x 70.9", electrically height adjustable, with sanitary appliances
Item number	R8683000

Mounting in different wall types

	<p>Concrete >B25</p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p>Solid Brick >= Mz12</p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p>Solid Sand Lime Brick >= Hlz12</p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p>Aerated Concrete P4</p> <p>V8658 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs GB14. To be ordered separately.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.</p>	



PRESSALIT®

Product Item number	Changing table, 31.5" x 70.9", electrically height adjustable, with sanitary appliances R8683000
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</p> <p>Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.</p>
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</p> <p>Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.</p>
	<p>Drywall (2 x 12,5 mm) water-resistant</p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p>

pressalit.com

Pressalit A/S
 Pressalitvej 1
 DK-8680 Ry
 Tel.: +45 8788 8788
 Fax: +45 8788 8789
 E-mail: pressalit@pressalit.com

PRESSALIT®