



# PRESSALIT®

<b>Product</b> <b>Item number</b>	Lift for countertop, electrically height adjustable RK1083-93
<b>Product description</b>	<p>EAN:5708590301389</p> <p>The name INDIVO relates to the individual configuration of the products.</p> <p>Electric lift for freestanding countertop. For countertops from 94.5" - 118.1". Height adjustable 11.8". Including 2 telescopic legs, brackets, longitudinal and cross braces and switch. Pressalit recommends overhang of 15.8" at either end of countertop to allow for ease of approach in wheel-chair. Please state desired length when ordering.</p>
<b>Adjustability</b> <b>Adjustment height</b> <b>Product capacity</b> <b>Speed up</b> <b>Noise level</b>	<p>Height adjustable</p> <p>11,82 inch</p> <p>Maximum load (evenly distributed): 220 lbs including countertop.</p> <p>Speed up: 0,79 inch/s Speed down: 0,79 inch/s</p> <p>45 dB</p>
<b>Materials</b>	<p>Material:</p> <p>Telescopic leg: Aluminium, ABS plastic Cross braces: Aluminium Brackets: Steel Cable tray: ABS plastic Switches: ABS plastic Surface treatment: Brackets: Powder lacquered (grey RAL 9006)</p>



<b>Product</b>	Lift for countertop, electrically height adjustable
<b>Item number</b>	RK1083-93
<b>Ergonomy</b>	<p>A freestanding electric Indivo solution is a flexible work or dining table, primarily intended for use in the kitchen.</p> <p>The height of the countertop can be quickly and easily adjusted to the given user or situation.</p> <p>A freestanding countertop can also be used in rooms in which the walls are not strong enough to support the wall-mounted models.</p>
<b>Features</b>	<p>Lift heights are adjusted via switches set in the edge or directly under the countertop. Operating switches can be placed anywhere.</p> <p>The design of the legs and feet make the table stable and secure, and ensure the lift causes minimal inconvenience to wheelchair users.</p> <p>The design of the lift makes it possible to use the countertop from all sides.</p> <p>Height adjustable over a range of 11.8".</p> <p>Available for countertops of any length between 55.1" and 11.8".</p>
<b>Mains connection (V)</b>	120
<b>Actuator (motor)</b>	DB4 Deskline (Linak) 1000 N, IP22
<b>Control box</b>	CBD4 (Linak) IP22
<b>Power consumption (maximum load)</b>	<p>Power consumption by maximum load: 300 W</p> <p>Power consumption by standby: 2 W</p>
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
<b>Cleaning</b>	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b> CaviCide</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b> Pressalit recommends that water deposits (Calcium, lime etc.) be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in plain water.</p>



# PRESSALIT®

<b>Product</b>	Lift for countertop, electrically height adjustable
<b>Item number</b>	RK1083-93

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

## PRESSALIT®