




# PRESSALIT®

---

**Pressalit wall mounted waste basket 411**  
**Wall-mounted waste basket incl. soft close**

---

|                         |   |   |
|-------------------------|---|---|
| <b>Item number</b>      | 411000<br>VVS:777740000<br>NRF:6190871<br>RSK:8980278<br>EAN:5708590212982<br><br>Pressalit waste basket - soft, round contours, practical, attractive and easy to clean solution (takes up no floor space!). Closes so softly (slowly) that it can be operated with one hand. The internal basket can be fitted with all types of plastic bags.  |  |
| <b>Color</b>            | White   |   |
| <b>Description</b>      | Pressalit wall mounted waste basket. Equipped with inner basket that holds a plastic bag and therefore is suitable for leaking/damp waste. Fully covering front in urea-duroplast with dampened self-closing function. Detachable front and inner basket to allow easier cleaning.  |   |
| <b>Designer</b>         | Pressalit   |   |
| <b>Design year</b>      | 2003  |   |
| <b>Materials</b>        | <b>WASTE BASKET:</b><br>The material is colour ingrained duroplast (UF A 10 = urea formaldehyde) that contains no environmentally hazardous substances. UF plastic comprises 67% urea formaldehyde resin, 28% cellulose, as well as 5% minerals, pigments, lubricants and moisture content. The raw material from the supplier contains up to 0.03% free formaldehyde and even less following curing.<br><br>Wall mount PA6 30% GF. Polyamide. (Glass-fibre reinforced nylon)<br>Suspension brackets PET/PBT 50% GF. Polyethylene terephthalate/Polybutylene terephthalate. (Glass-fibre reinforced thermoplastic polyester)<br>Inner basket ABS (Acrylonitrile-butadiene-styrene). |   |
| <b>Product capacity</b> |   |   |



# PRESSALIT®

---

**Pressalit wall mounted waste basket 411**  
**Wall-mounted waste basket incl. soft close**

---

|                          |  |
|--------------------------|--|
| <b>Weight</b>            | 2,5 kg   |
| <b>Carton size</b>       | 443x318x126 mm   |
| <b>Gross weight</b>      | 2,88 kg  |
| <b>Weight per crate</b>  | 2,88 kg  |
| <b>Qty per crate</b>     | 1  |
| <b>Crates per pallet</b> | 48   |
| <b>Qty per pallet</b>    | 48   |
| <b>Cleaning</b>          | This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.  |
| <b>Warranty</b>          | <p>Pressalit provides a 10-year product warranty on your product. Pressalit will repair or exchange the product for the same or another useable model, at Pressalit's discretion, in the event of a material or manufacturing defect in your product appearing within 10 years of the date of purchase with normal use. This product warranty is conditional upon proof of purchase of the product.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p> |

---

[pressalit.com](http://pressalit.com)

---

PRESSALIT®