



# PRESSALIT®

---

**Pressalit folding seat 412**  
**Wall-mounted folding seat incl. hinge in stainless steel**

---

**Item number**

412000  
VVS: 777510000  
NRF: 6190881  
RSK: 7904523  
EAN: 5708590212944

Pressalit folding seat - soft, round forms and soft close.  
An extra seat in the bathroom, in the stairway or maybe  
in the hall?  
The folding seat is not suitable for  
use in the shower or any other facilities where the folding  
seat is exposed to water.

**Color**

White

**Description**

Pressalit wall-mounted folding seat no. 412 with  
damping, made from color ingrained duroplast  
including stainless steel hinge for versatile applications  
in private homes and institutions. An extra seat when  
in use, and discrete, yet elegant when folded (with  
damper) against the wall. The folding seat is not  
suitable for use in the shower or any other facilities  
where the folding seat is exposed to water.  
- load 125 kg/275 lbs  
- 10 year guarantee

---

**Designer**

Pressalit

**Design year**

2003

---



---

**Pressalit folding seat 412**  
**Wall-mounted folding seat incl. hinge in stainless steel**

---

|                          |   |
|--------------------------|---|
| <b>Materials</b>         | <p>FOLDING SEAT:</p> <p>The material is colour ingrained duroplast (UF A 10 = urea formaldehyde) that contains no environmentally hazardous substances. UF plastic comprises 67% urea formaldehyde resin, 28% cellulose, as well as 5% minerals, pigments, lubricants and moisture content. The raw material from the supplier contains up to 0.03% free formaldehyde and even less following curing.</p> <p>Wall mount stainless steel (V2A) Type W no. 1.4308</p> <p>Support stainless steel (V2A) Type W no. 1.4308</p> <p>Striker plate stainless steel (V2A) Type W no. 1.4301</p> <p>Shaft stainless steel (V2A) Type W no. 1.4301</p> <p>Handle PA66 30% GF. Polyamide (glass-fibre reinforced nylon)</p> <p>Damper make/model TOK model TD 58</p>   |
| <b>Product capacity</b>  | Load - ring seat 125 kg   |
| <b>Weight</b>            | 4,2 kg  |
| <b>Carton size</b>       | 390x382x85 mm   |
| <b>Gross weight</b>      | 4,62 kg   |
| <b>Weight per crate</b>  | 4,62 kg   |
| <b>Qty per crate</b>     | 1   |
| <b>Crates per pallet</b> | 60  |
| <b>Qty per pallet</b>    | 60  |
| <b>Cleaning</b>          | <p>Use a mild soap solution to clean the seat. Please take care that the seat and hinges are not left damp. Dry off any residual water or cleaning agent with a soft cloth. Avoid contact of the seat and hinges with abrasive, corrosive or chlorine-based cleaners, as these may cause damage or lead to flash rust. Therefore, when cleaning the bowl, make sure that the seat and cover are kept in an upright position until all cleaning agent has been flushed away.</p>   |
| <b>Warranty</b>          | <p>Your Pressalit toilet seat is subject to a 10-year product warranty against presentation of receipt. You should contact the dealer or store where you purchased the seat in the event of a complaint.</p> <p>In the event of complaints about defective materials and/or manufacturing defects and/or functional limitations ascertained within a 10-year period, following proper use and cleaning of the toilet seat (we reserve the right to examine the toilet seat at our factory), Pressalit will deliver spare parts or replace the toilet seat by an identical or similar model. If the color is no longer available, Pressalit reserves its right to replace the toilet seat by a similar model in the color white. Upon replacement or delivery of a spare part, the warranty period will not be extended nor renewed. If replacement is not possible, Pressalit may instead refund the purchase price.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p> |



# PRESSALIT®

---

**Pressalit folding seat 412**  
**Wall-mounted folding seat incl. hinge in stainless steel**

---

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®